

Botron B7023 Technical Data Sheet



Overview:

Type S Vinyl Anti-Fatigue floor mats provide excellent electricals, and durability. It exceeds both EOS/ESD and department of defense requirements. Available in Gray and Brown runners, and pre cut floor mats with hardware.

FINAL TEST^{MR}
Venta de Instrumentos de Prueba y Medición
Calle del Ebano #16625
Jardines de Chapultepec
Tijuana B.C. Mexico
Tel. (664) 681 1130
Fax. (664) 681 1150
Tel. 01800 027-4848
www.finaltest.com.mx

Product Notes and Features

- Anti-Fatigue Design
- Beveled Edge
- Non-skid Backing
- Pebble Embossed Surface Texture
- Lead-Free RoHS Compliant

PROPERTIES	SPECIFICATIONS
------------	----------------

Material:	.375" Thick Vinyl/Foam Construction
Meets Standards:	Dissipative Top Layer ANSI EOS/ESD S4.1 RTG Fed Std 101 Method 4046
Electricals:	Top layer <10 ¹⁰ RTT (Resistance Top to Top) <10 ¹⁰ Ohms RTG (Resistance to Ground) <10 ¹⁰ Ohms Charge Decay Time 5000 volts to 50v <0.01 Seconds
Colors:	Brown, Gray

AVAILABLE APPLICATIONS

- 60' Runners
- Standard 3 x 5 Floor Mats with Beveled Edge



INSTALLATION

1. Unroll mat.
2. Attach 10' common point ground B9702 to 3/8" snap on mat.
3. Connect opposite end of wire to ground.
4. Check with your facility people for building ground.

TESTING GUIDELINES

Botron recommends testing ESD mats with the following test equipment: B8582, B8572, B8563, B8560, BSRM6, BSRM10.

Using two 5lbs. weights, placing them approximately 18" apart, conduct the test according to the test equipment which you are using.

Conduct this test to achieve a reading for RTG (resistance to ground) and RTT (resistance top to top) respectively.

When using the BSRM6 and BSRM10, simply place on top of surface of mat and hold down test button to achieve a surface resistance reading.

*Please note, it is recommended to read the testing guidelines provided with the ESD Tester you are using.

PART NUMBERS

BF435 3' x 5' Gray anti-fatigue mat w/snap and ground
BF335 3' x 5' Brown anti-fatigue mat w/snap and ground
BF436 3' x 60' Gray anti-fatigue runner
BF336 3' x 60' Brown anti-fatigue runner

GROUNDING

All pre-cut mats come with attached snap and one B9701 floor mat ground. B9701 when properly setup will provide a grounded area for use with heel and toe grounds. For grounding rolls please see hardware (each mat will need a snap and ground to be effective).